


920i® Wall Mount Indicator/Controller

Bottom View

Part Number/Price

Ref#	Part#	Description	Price
37	32365	Set-up switch access screw, 1/4 x 20 NC x 1/4	Consult
38	59250	Sealing washer for set-up switch access screw	Consult
39	30376	Nylon seal rings for 1/2 NPT Cord-grips	Consult
40	15628	Cord-grips, 1/2 NPT	Consult
42	71447	Machine screws, 1/4 - 28 NF x 3/4 Phillips	Consult
	71455	Machine screw, 1/4-28 NFX x 3/4, drilled fillister	Consult
	71739	Clip, clinching	Consult
43	71462	Fuses F1 and F2 (115 VAC and 230 VAC North American models), 3.15 A Time-Lag TR5	Consult
	72339	Fuses F1 and F2 (230 VAC European models), 3.15 A Time-Lag TR5	Consult

(See Diagram 920i-K)



920i-K

INDICATORS

920i® Wall Mount Indicator/Controller


CPU Board & Power Supply Connections



Part Number/Price

Ref#	Part#	Description	Price
	71781	34 pin flat cable, 16"	Consult
	71780	34 pin flat cable, 23.5"	Consult
9	67795	Power cord assembly, 115VAC and 230VAC North American units	Consult
	69998	Power cord assembly, 230VAC European units	Consult
13	14822	Machine screws, 4 - 40 NC x 1/4	Consult
28	71431	Power supply cable assembly, to CPU board	Consult
29	71436	Ribbon cable to interface board	Consult
44	71333	Power supply, VAC, 65W	Consult
	97474	DC/DC converter, 9-36 VDC, +/-6 VDC 25W	Consult
46	70069	3V Lithium coin battery	Consult
47	68532	Single-channel A/D card option	Consult
	68533	Dual-channel A/D card option	Consult
	87697	Analog input and thermocouple	Consult
	67600	Memory, 1 MB NV RAM option	Consult
	67601	Digital I/O, 24-channel option	Consult
	67602	Analog output: selectable 0-10V, 0-20 mA option	Consult
	103138	Analog output, dual channel 0-10VDC, 0-20 mA option	Consult
	67604	Serial, dual channel option	Consult
	67603	Pulse input, single channel option	Consult
	68541	DeviceNet™ interface option	Consult
	68539	Allen-Bradley® Remote I/O interface option	Consult
	68540	Profibus® DP interface option	Consult
	103136	Control net interface option	Consult
	87803	EtherNet/IP (for A-B PLC)	Consult
	71986	Ethernet TCP/IP 10/100 Base-T module (internal) option	Consult
	69782	Option, 2-Slot Expansion Board, (Wall Mount)	Consult
	69808	Board assembly, Expansion 2-Slot	Consult
	71757	Cable assembly, DC Power, CPU and Expansion	Consult
	71780	Cable assembly, Ribbon 23 inch	Consult
	69783	Option, 6-Slot Expansion Board, (Wall Mount)	Consult
	69809	Board assembly, Expansion	Consult
	71759	Cable assembly, DC Power to Expansion, 27 inch	Consult
	71781	Cable assembly, Ribbon 16 inch	Consult
	87164	Cable assembly, Ribbon 5.5 inch	Consult
50	117930	CPU board green solder mask	Consult
50	186272	CPU board blue solder mask	Consult

The LED backlight display can be used with green CPU board Rev N or older by replacing the power supply cable. Universal 186464 (AC) 186464 (DC); Deep universal 186278 (AC) 187603 (DC); Panel 186278 (AC) 187603 (DC); Wall 186760 (AC) 188345 (DC); Two-slot expansion for wall 188716 (AC) 189724 (DC); Two-slot expansion panel for deep universal 188717 (AC) 189725 (DC); Six-slot expansion for wall 188774 (AC).
(See Diagram 920i-L)



920i-L