

# FX-iWP Series Washdown

## Standard Features

- Washdown IP65 rating
- Compact Super Hybrid Sensor Technology (SHS)
- Vacuum Fluorescent Display (VFD)
- GLP/GMP/ISO compliant to either AD-8121 printer or computer. Transmits date, time, ID number, serial number and calibration data.
- RS-232 interface for connecting to printer or PC
- Response indicator function
- Under weigh hook

## Specifications

### Weighing Units:

Pound, Carat, Pennyweight, Troy Ounce, Grain, Pound/Ounce

### Operating Modes:

Weigh, Count, Percent, Animal Weighing, Statistical, Hold and Comparator

### Power:

120/240 VAC adapter, approx. 11 VA

### Stabilization Time:

Approx. 1 second

### Sensitivity Drift (10 °C to 30 °C):

±2 ppm/°C

### Display Refresh Rate:

5 times/second, 10 times/second or 20 times/second

### Calibration Weight:

FX-120iWP: 100 g  
FX-200iWP: 200 g  
FX-300iWP: 300 g

### Operating Temperature:

41 °F to 104 °F (5 °C to 40 °C) 85% RH or less (no condensation)

### Est. Weight:

8 lb (3.5 kg)

### Warranty:

Five-year limited

### Return Policy:

A&D Weighing standard policy - restock fee may apply

Model	Capacity	Readability	Repeatability	Linearity	Pan Size	Dimensions	Part #	List Price
FX-1200iWP	1,220 g	0.01 g	0.01 g	±0.02 g	Ø 5.90 in (150 mm)	6 × 10.3 × 3.3 in (193 × 263 × 85 mm)	102908	Consult
FX-2000iWP	2,200 g	0.01 g	0.01 g	±0.02 g	Ø 5.90 in (150 mm)	6 × 10.3 × 3.3 in (193 × 263 × 85 mm)	102909	Consult
FX-3000iWP	3,200 g	0.01 g	0.01 g	±0.02 g	Ø 5.90 in (150 mm)	6 × 10.3 × 3.3 in (193 × 263 × 85 mm)	102910	Consult

## Options/Accessories

Part #	A&D Model #	Description	Price
98027*	FXi-02	Quick USB interface	Consult
98028*	FXi-08	Ethernet interface with WinCT© Plus software	Consult
98029*	FXi-09	Built-in rechargeable battery	Consult
98030	FXi-10	Small breeze break	Consult
98031	FXi-11	Large breeze break	Consult
97649	TB:648	AC adapter (120 V/220 V)	Consult

\*Options FXi-02/FXi-08 and FXi-09 cannot be combined and are factory installed only.

